


NG 5 RECTIFIER UNIT 1-PHASE


IN: 41VAC OUT: 24V/5A

INPUT: max. 41 V AC

Output rating: 120 W

Current: max. 5 A

[Link to Product](#)**Illustration**



Product may differ from Image

Input

Input voltage	max. 5...44 V AC
Input current	max. 5 A; 4 A (+60 °C)
Input fuse (external)	8 A (T), 5 × 20 mm
Frequency	45...65 Hz

General data

Mounting method	DIN-rail mountable TH35 (EN 60715)
Dimensions H × W × D	90×68×87 mm
Temperature range	-20...+60 °C

Output

Output voltage	U-IN × 1.16/max. 60 V DC
Output current	max. 5 A; 4 A (+60 °C)
Ripple	max. 5 %rms
Output filter	smoothed with smoothing capacitor and LED

Commercial data

country of origin	CZ
customs tariff number	85044082
minimum order quantity	1