

## Hose Tail Adaptor

Connects hose to a female fitting.



PART NUMBER	MALE THREAD	HOSE INTERNAL DIAMETER
HC1205	R 1/4	4.75 mm / 3/16 in
HC5656	R 1/4	6.35 mm / 1/4 in
HC1206	R 1/4	7.9 mm / 5/16 in
HC1217	R 1/4	9.5 mm / 3/8 in
HC2479	R 1/4	12.7 mm / 1/2 in
HC6904	R 3/8	6.35 mm / 1/4 in
HC6905	R 3/8	7.9 mm / 5/16 in
HC2951	R 3/8	9.5 mm / 3/8 in
HC2808	R 3/8	12.7 mm / 1/2 in
HC6908	R 1/2	9.5 mm / 3/8 in
HC2954	R 1/2	12.7 mm / 1/2 in
HC9336	1/4 NPT	6.35 mm / 1/4 in

## Coned Tailpiece

Connects hose to a male fitting.



PART NUMBER	UNION NUT SIZE	HOSE INTERNAL DIAMETER
HC5030	R 1/4	4.75 mm / 3/16 in
HC5275	R 1/4	6.35 mm / 1/4 in
HC5276	R 1/4	7.9 mm / 5/16 in
HC1225	R 1/4	9.5 mm / 3/8 in
HC2595	R 3/8	6.35 mm / 1/4 in
HC2594	R 3/8	7.9 mm / 5/16 in
HC2192	R 3/8	9.5 mm / 3/8 in

## Union/Swivel Nut

Union/Swivel Nut for various connection types.



PART NUMBER	FEMALE THREAD	SUITABLE FOR	CONED TAILPIECE PART NUMBER
HC5194	Rp 1/4	4.75 mm / 3/16 in to 7.9 mm / 5/16 in	HC5030, HC5275, HC5276
HC1226	Rp 1/4	9.5 mm / 3/8 in	HC1225
HC2181	Rp 3/8	6.35 mm / 1/4 in to 9.5 mm / 3/8 in	HC2192, HC2594

## Coned Tailpiece & Union Nut



### FEATURES

Swivel nut and hose tail combinations Female swivel hose tail adaptors/connectors

PART NUMBER	FEMALE THREAD	HOSE INTERNAL DIAMETER
HC5194 + HC5030	R 1/4	4.75 mm / 3/16 in
HC5275/5194	R 1/4	6.35 mm / 1/4 in
HC5276/5194	R 1/4	7.9 mm / 5/16 in
HC1226 + HC1225	R 1/4	9.5 mm / 3/8 in
HC2595/HC2181	R 3/8	6.35 mm / 1/4 in
HC2181 + HC2594	R 3/8	7.9 mm / 5/16 in
HC2192/2181	R 3/8	9.5 mm / 3/8 in