


ID Cable Ties

- ID tab allows for easy identification.
- For indoor use.




Length A	Part #	Pkg Qty	DoubleLock®	Tensile Strength	Width B	Thickness C	Bundle Dia. Max.	UL	Color
8"	45-308ID	25/bag	—	50 lb	0.17"	0.05"	2"	—	Natural



Colored Cable Ties

Colored cable ties fasten wire for easy bundle identification.

- Patented DoubleLock® design ensures 50% more tensile strength than industry standards.
- Flexible nylon material allows cable ties to remain serviceable through temperature ranges of -40 to 185 °F (-40 to 85 °C).
- Recognized under component program of UL, E125869.
- Meets flammability classification UL 94 V-2.



Length A	Part #	Pkg Qty	DoubleLock®	Tensile Strength	Width B	Thickness C	Bundle Dia. Max.	UL	Color
8"	45-308FB	20/bag	✓	75 lb	0.17"	0.055"	2"	UR	Flr Blue
	45-308FG	20/bag	✓	75 lb	0.17"	0.055"	2"	UR	Flr Green
	45-308FY	20/bag	✓	75 lb	0.17"	0.055"	2"	UR	Flr Yellow
	45-308G	20/bag	✓	75 lb	0.17"	0.055"	2"	UR	Green
	46-308G	100/bag	✓	75 lb	0.17"	0.055"	2"	UR	Green
	46-308FST	100/bag	✓	75 lb	0.17"	0.055"	2"	UR	Asst.
	46-ACL	120/bag	✓	75 lb	0.17"	0.055"	2"	UR	Asst.
	46-ACT	100/bag	✓	75 lb	0.17"	0.055"	2"	UR	Asst.



Stainless Steel Cable Ties

- 304 Stainless Steel design for harsh, corrosive, and salt-water environments.
- Resists chemicals and radiation exposure as well as enduring extreme temperatures.
- Stainless steel is great for clean environments such as food processing areas.
- Self-locking ball mechanism meets low insertion force requirements while maintaining high tensile strength.

Length	Part #	Pkg Qty	Tensile Strength	Bundle Dia. Max
6"	45-306SS	10/bag	100 lb	1.5"
11"	45-312SS	10/bag	100 lb	3.75"