

Drawer cabinets

Mobile with a pair of roller carriers and nylon rollers Ø 100 mm

Application:

For day-to-day heavy-duty use in workshops

Version:

- All drawers with full extension
- Individual drawer lock as standard feature to prevent the cabinet from tipping over
- Perforated, slotted drawers provide a secure hold
- Very robust construction for a wide variety of applications and very demanding requirements

Advantage:

- Optimum wall height to keep items from falling out and getting lost
- Folding handle strips for simple, clean and protected labelling
- High quality - made in Germany and Swiss-made
- Runs perfectly smoothly and easily due to the lack of crossbars on the differential extension slide
- Full extension - clear view and optimal access

Delivery:

1 anti-roll-off edging, 4-sided, 1 sliding rod, 1 roller carrier pair with nylon rollers, Ø 100 mm



| | |
|--|-----------------------------------|
| Art. no. | 50300 117 |
| Number of drawers | 4 PCS |
| Height | 723 mm |
| Width | 411 mm |
| Depth | 572 mm |
| Height x width x depth | 723 x 411 x 572 mm |
| Housing height | 533 mm |
| Draw width (inner dimension) x drawer depth (inner dimension) | 300 x 450 mm |
| Load-carrying capacity per drawer | 75 kg |
| Drawer lock | Single lock right |
| Drawer front height | 1 x 50 mm, 1 x 100 mm, 2 x 150 mm |
| Cabinet colour | Light blue RAL 5012 |
| Colour of front | Light blue RAL 5012 |
| Cabinet equipment | Pair of castors |
| With sliding handle | Yes |
| Height of roller carrier pair | 137 mm |
| Wheel diameter | 100 mm |
| Material of wheel | Nylon (polyamide) |
| Information about the direction | Along |
| Load-carrying capacity of roller | 400 kg |
| Opening/closing system | Key Lock |
| Rim height | 53 mm |
| Clear height | 450 mm |
| LISTA unit | 18 x 27 E |

EAN-Code

7612269077001