


Standardverschraubungen »value line«

- Messing vernickelt -

Für Luft, Wasser, Dampf, Öl etc.

max. Betriebsdruck: 60,0 bar
 max. Betriebstemperatur: 150 °C



252.23/N-E

Muffen

Artikel Nr.	Ident Nr.	F	H	CH
252.20/N-E	115661	M5	11,0	8
252.21/N-E	115662	G 1/8	15,0	14
252.22/N-E	115663	G 1/4	22,0	17
252.23/N-E	115664	G 3/8	23,0	22
252.24/N-E	115665	G 1/2	28,0	26
252.25/N-E	115666	G 3/4	32,0	32