

HSSE Co 5 narrow disc milling cutter

Type N

ORION[®]

Application:

For slot milling and cutting

Version:

- Type D
- Coarse cross-toothing
- Cutting on 3 sides
- Bore with longitudinal groove to DIN 138



| Application | Steel (N/mm ²) | | | Stainless steel | | Alu | | Brass | | Bronze | | Plas-tics | Graphite G(C)FK | GG(G) GjMW | Titan-alloy | Nickel-alloy | Super-alloy | Hard mat. | |
|-------------|----------------------------|-------|-------|-----------------|---------|-------|------|-------|------|--------|------|-----------|-----------------|------------|-------------|--------------|-------------|-----------|---------|
| | <700 | <1000 | <1300 | marten. | austen. | short | long | short | long | short | long | | | | | | | <55 HRC | <65 HRC |
| | 27 | 22 | 17 | 20 | 11 | 195 | 195 | 160 | 170 | 30 | 30 | 183 | | 23 | 18 | 18 | 10 | | |

| | |
|---------------------------------------|------------------|
| Art. no. | 14105 310 |
| Type | N |
| Number of cutting edges | 16 PCS |
| Milling cutter design standard | DIN 1834 |
| Cutting edge diameter | 63 mm |
| Bore diameter | 22 mm |
| Width of cutting edge | 2 mm |
| fz steel 700 | 0.02 mm |

EAN-Code

4053625035243