

QUICK CAB PCQ 303017 T



Sample photo

Order symbol: CAB PCQ 303017 T
Product nbr: 8113048
Description: Cabinet, PC
Remarks: Smoked transparent cover

EAN: 6418074011084
EI. number:
 Finland: 3421922
 Electric No. Italy: 7682030
 Electric No. Sweden: 2539184

Including: Base with screws for mounting plate/DIN-rail, internal corner plugs, cover with PUR gasket and CS 12137 cover screws.

Dimensions:		Length	Width	Height	Accessories:		
mm:		300	300	170	EKIV 27	DIN-35 Mounting rail	
inch:		11.8	11.8	6.7	FP A 33	Swing-out door/Front plate	
Materials:						MB 12225 AL	Swing door set
Material:		Polycarbonate			FP 12-33	Front plate	
Base colour:		RAL 7035 -light grey			FP 12x2-33	Front plate	
Cover screws material:		Polyamide			DRF 33	DIN rail frame set	
Cover colour:		Smoked grey			PAT 12040	Hinge set	
Cover screws colour:		RAL 5023			Rating:		
Gasket material:		Polyurethane			Ingress Protection (EN 60529): IP66/IP67		
Temperatures:						Impact Resistance (EN 62262): IK08	
Temperature °C (short term):		-40 ... 120 °C			Electrical insulation: Totally insulated		
Temperature °C (continuous):		-40 ... 80 °C			Halogen free (DIN/VDE 0472, Part 815): 1		
Temperature °F (short term):		-40 ... 250 °F			UV resistance: UL 508		
Temperature °F (continuous):		-40 ... 175 °F			Flammability Rating: UL 746C 5"		
Accessories:						Glow Wire Test (IEC 695-2-1) °C: 960	
		EKIV 33			NEMA Class: NEMA 1, 4, 4X, 12, 13		
		Mounting plate			Certificates:		
						SGS Fimko	

