

Slides DZ 3832, Width 12.7 mm, to 50 kg, Full Extension

Material:

Slide elements: Cold-rolled steel, bright zinc-plated.

Ball retainers: Plastic / zinc-plated steel.

Balls: Hardened steel.


Telescopic ball bearing slides for applications in the industrial and electronics sector.

- Fast disconnection.
- Hold-in in closed position.
- Can be mounted on both sides.
- Cam drawer adjust (3.1 mm).
- Optional clip-on bracket (page 630).
- Service life 80,000 cycles.
- Temperature range: -20°C to +70°C.

Ordering Details: e.g.: Product No. 649 012 15, Slides DZ 3832




Accuride



Product No. per Pair	Slide Length mm	Travel +/-3.2 mm	Load Rating per Pair kg	Weight per Pair kg
649 012 15	148	138	45	0,44
649 012 20	199	203	46	0,60
649 012 25	250	254	47	0,76
649 012 30	300	305	48	0,90
649 012 35	350	356	49	1,06
649 012 40	400	406	50	1,22
649 012 45	450	457	50	1,36
649 012 50	500	508	50	1,52
649 012 55	550	559	50	1,68
649 012 60	600	610	50	1,85
649 012 65	650	660	49	2,00
649 012 70	700	711	48	2,15

Optional Clip-On Brackets see page 630.



Slide Length mm	Travel +/-3.2 mm	A mm	B mm	C mm	D mm	E mm	F mm	G mm	H mm	J mm	K mm
148	140	-	-	-	-	-	-	77,2	-	-	-
199	203	128	-	-	-	-	141	128	-	-	-
250	243	96	-	-	-	-	192	128	-	-	-
300	305	96	-	-	-	-	242	128	224	-	-
350	356	128	-	-	-	-	292	128	224	-	-
400	406	128	-	-	-	-	342	128	224	320	-
450	457	128	-	-	320	-	392	128	224	352	-
500	508	128	-	-	320	-	442	128	224	416	-
550	559	128	-	-	320	416	492	128	224	352	448
600	610	128	224	-	416	-	542	128	224	352	480
650	660	128	224	-	416	544	592	128	224	352	544
700	711	128	224	288	416	544	642	128	224	352	544

Note

Recommended mounts: M4 screw.

Use all mounting positions to achieve the max. load rating. Horizontal mounting not recommended.