

electronic pocket Vernier callipers

TESA-CAL IP67

 TESA

Application:

For measuring external, internal, step and depth dimensions.

Execution:

- With locking screw
- ON
- mm/inch changeover
- AUTO OFF
- Zero setting at any position
- ABS function

Advantage:

- Long operating time of over 12,000 hours

Delivery:

In a case, with battery (1x 3 V lithium, type CR 2032)



Art. no.	31172 202
Brand	TESA
Manufacturer Part Number	00530142
Min./max. length measuring range	0-200 mm
Depth gauge rod	Flat
IP protection class	IP 67
With drive wheel	Yes
Length of jaw	50 mm
Digit height	11 mm
Length of cross tips	20 mm
Digit increment	0.01 mm
Digit increment in inches	0.0005 in
Type of locating	With locking screw
Battery designation	3V CR2032 Lithium
Number of rechargeable batteries/batteries	1 PCS
Weight of rechargeable battery/battery	0.003 kg
Battery voltage	3 V
Type of rechargeable battery/battery	Lithium
Calibration Group	A
ISO	13385-1
Type	TESA-CAL IP67
Gross Weight	0.470 kg
Product Group	362

EAN

7630041148657