

## LED cold light source F1

With a light output of up to 335 lm



### Application:

Fibre optic light source impresses with its excellent light output. Ideal for stereomicroscopic and endoscopic inspection tasks requiring good illumination. Due to the low heat generation, also suitable for heat sensitive objects.

### Execution:

- Robust metal housing
- Long-lasting, energy-efficient LED light source
- Fanless, thus no vibrations
- Infinitely variable brightness regulation
- ESD connector

### Advantage:

- High light density over a small surface
- absolutely silent and vibration-free



<b>Art. no.</b>	<b>41613 635</b>
<b>Brand</b>	PHOTONIC
<b>Manufacturer Part Number</b>	10030
<b>Model</b>	F1
<b>Lamp type</b>	LED
<b>Colour temperature</b>	5500 K
<b>ESD bush</b>	Yes
<b>Life time of illuminant</b>	50000 h
<b>Input voltage</b>	24 V/DC
<b>Min./max. nominal voltage</b>	100 / 240 V/DC
<b>Gross Weight</b>	3.000 kg
<b>Product Group</b>	412