

## Electronic dial gauge

MarCator 1087 R



### Application:

For static and dynamic measurements of lengths and length differences, e.g. concentricity, flatness, position measurements.

### Execution:

- Factor adjustable
- mm/inch switch-over
- LOCK function (key lock)
- Permissible deviation MPEp 2 µm

### Delivery:

In case with CR 2450 battery



<b>Art. no.</b>	<b>33166 630</b>
<b>Brand</b>	MAHR
<b>Manufacturer Part Number</b>	4337660
<b>Length measuring range</b>	12.5 mm
<b>Digit increment</b>	0.0005 mm
<b>Min./max. measurement force</b>	0.65-0.9 N
<b>Error limit</b>	4 µm
<b>Repeat accuracy</b>	1 µm
<b>Data transmission type</b>	multiCOM
<b>IP protection class</b>	IP 42
<b>Absolute function</b>	Yes
<b>Automatic switch-off</b>	Yes
<b>Dynamic measurement</b>	Yes
<b>Preset function</b>	Yes
<b>Tolerance value entry</b>	Yes
<b>Number of rechargeable batteries/batteries</b>	1 PCS
<b>Rechargeable battery/battery capacity</b>	540 mAh
<b>Battery voltage</b>	3 V
<b>Weight of rechargeable battery/battery</b>	0.0059 kg
<b>Battery designation</b>	3V CR2450N lithium
<b>Rotating housing</b>	Yes
<b>Combined indicator for figure/scale reading</b>	Yes
<b>Reversible counting direction</b>	Yes
<b>Calibration Group Description</b>	Dial gauge
<b>Calibration Group</b>	CE
<b>Gross Weight</b>	0.294 kg
<b>Product Group</b>	305

### EAN

4059192014629