


RMI 24V AC/DC OUTPUT RELAY

IN: 24 VAC/DC - OUT: 250 VAC/DC / 15 A

1 relay; 1 NO/NC contact
15 A
24 V AC/DC
Screw terminals

[Link to Product](#)

Illustration



Product may differ from Image

Utilization category

AC-15	6 A (24 V AC; 230 V AC)
AC-1	15 A (24 V AC; 230 V AC)
DC-13	2 A (24 V DC); 0.3 A (230 V DC)

Input

Connection voltage - current	21.6...26.4 V AC/DC
LED display	red

General data

Mech./ elect. life	20.000.000 switching cycles/load dependent
Test isolation voltage	6 kV
Mounting method	DIN-rail mountable TH35 (EN 60715)
Temperature range	-25...+60 °C (storage temperature -40...+80 °C)

Output

Switching voltage	max. 250 V AC/DC
Switching current per output	max. 15 A
Min. load current	100 mA
Power rating (voltage dependent)	max. 4000 VA/240 W
Switching frequency	max. 0.1 Hz (with load)
Contact material	Ag Ni
Energize/release/contact bounce time	10/15/2 ms

Commercial data

country of origin	CZ
customs tariff number	85364900
minimum order quantity	1