

## Steel construction clamps STBM, 300–800 mm clamping width

Heavy-duty design, T-handle




### Application:

For powerful clamping of a range of workpieces.

### Execution:

- Movable locking handle
- Fixed part in tempered steel
- Sliding bar in forged tempered steel
- Tempered spindle
- Clamping force up to 22,000 N



<b>Art. no.</b>	<b>51120 060</b>
<b>Brand</b>	BESSEY
<b>Manufacturer Part Number</b>	STB60M
<b>Max. clamping width</b>	600 mm
<b>Overhang</b>	175 mm
<b>Rail cross-section L x W</b>	40 x 20 mm
<b>Material of handle</b>	Steel
<b>Gross Weight</b>	8.000 kg
<b>Product Group</b>	517

### EAN

4008158007649