

## Mini pneumatic rod grinder 9032M-36

224 W




### Application:

For precise machining of workpieces even in extremely cramped conditions

### Execution:

- 6-mm chuck with 3-mm adapter to accommodate both sanding block sizes



<b>Art. no.</b>	<b>75038 040</b>
<b>Brand</b>	HAZET
<b>Manufacturer Part Number</b>	9032M-36
<b>Model</b>	9032M-36
<b>Design</b>	MINI
<b>Max. idle speed</b>	30000 rpm
<b>Power output</b>	224 W
<b>Air consumption</b>	43.7 l/min
<b>Connection thread</b>	G 1/4 inch
<b>Inner hose diameter</b>	5 mm
<b>Length</b>	150 mm
<b>Operating pressure</b>	6.3 bar
<b>Weight</b>	0.38 kg
<b>Gross Weight</b>	0.605 kg
<b>Product Group</b>	738

### EAN

4000896209606