



RE526-HP

- SRBP paper FR2 1.50 mm
- Single-sided 35 µm Cu
- Organic soldering protection (OSP)
- Component print
- Hole spacing 2.54 x 2.54 mm
- 36 continuous strips with 56 holes
- Hole diameter 1.00 mm
- Connector DIN 41612 Typ H 15-channel hole spacing 5.08 mm
- Size 100 x 160 mm