

Angular milling cutter HSSE Co 5


ORION[®]

Application:

For milling ducts and other angular geometries in tool and mechanical engineering.

Execution:

- Straight-grooved
- Finely toothed
- Straight shank according to DIN 1835 B.
- For cutting on periphery and end face



Art. no.	15814 040
Brand	ORION
Manufacturer Part Number	15814040
Cutting material	HSSE Co5
Type	N
Number of cutting edges	10 PCS
Chamfer angle	45 Degree
Tool holding device	HB parallel shank
Cutting edge diameter	25 mm
Width of cutting edge	6.3 mm
Immersion depth	22 mm
Length	67 mm
Shank diameter	12 mm
Form	C
fz steel 700	0.06 mm
Gross Weight	0.030 kg
Product Group	106

EAN

4039247098095