

Waterproof ExStik[®] II Dissolved Oxygen Meter/Kit







Easy to replace screw on membrane cap
For fast replacement and operation. Extension cable and weighted probe guard included with the Kit

Features:

- Convenient kit adds versatility on measuring Dissolved Oxygen in laboratories or out in the field with a 16ft (5m) extension cable and probe weight guard for taking easy measurements in tanks or streams
- Oxygen level displayed as % Saturation from 0 to 200.0% or Concentration from 0 to 20.00ppm (mg/L)
- Adjustable Altitude Compensation (0-20,000ft in 1,000ft increments)
- Adjustable Salinity Compensation from 0 to 50ppt
- Analog bargraph indicates trends
- Memory stores up to 25 data sets with DO and Temperature reading
- Self calibration on power up
- Data Hold, Auto power off, Low battery indicator
- Waterproof to IP57
- Optional 3 ft (1m) or 16ft (5m) extension cable with probe weight.
- DO600 meter includes DO electrode, protective sensor cap, spare membrane cap, electrolyte, four 3V CR-2032 batteries, and 48" (1.2m) neckstrap. See image on right for DO600-K Kit information.



DO600-K — Kit includes DO600 meter, DO603 membrane kit, 16ft (5m) extension cable, weighted probe guard, and hard carrying case — \$125 savings

		
Sample testing with extension cable attached to meter	Sample testing with the meter in a laboratory environment	Choice of optional 3ft (1m) or 16ft (5m) extension cable with probe weight
		
Extension cable attached to meter	Bonded membrane cap for easy replacement	DO603 Membrane Kit includes 6 screw on membrane caps, 15mL filling solution and polishing paper

Specifications	Range	Max Resolution	Basic Accuracy
DO (saturation mode)	0 to 200.0%	0.1%	±2% FS
DO (concentration mode)	0 to 20.00ppm (mg/L)	0.01ppm (mg/L)	0.4ppm (mg/L)
Temperature	32 to 122°F (0 to 50°C)	0.1°F/°C ±1.8°F (1°C)	
Dimensions	1.4x6.9x1.6" (36x176x41mm)		
Weight	3.8oz (110g)		

Ordering Information:

- DO600**ExStik[®] II Dissolved Oxygen Meter
DO600-KExStik[®] II Dissolved Oxygen Kit
DO610ExStik[®] II DO/pH/Conductivity Kit
DO603Membrane Kit for DO600 and DO605
DO605Spare ExStik[®] II Dissolved Oxygen Electrode module
EX010Extension Cable, 3ft (1 Meter) with probe weight for ExStik
EX050Extension Cable, 16ft (5 Meter) with probe weight for ExStik
CA895Carrying case, Small with Belt Loop
CA903Carrying case for ExStik[™] kit

