

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **0484060003**  
**Status:** **Active**  
**Overview:** USB Connectors: USB Type-A, USB Type-B, and USB Type-C Plugs and Receptacles  
**Description:** Universal Serial Bus (USB 3.0) I/O Receptacle, Dual Port Stacked, Right-Angle, Type A, High-Temperature Blue Nylon, 0.38µm Gold (Au) Plating, Contact Height 4.13mm

**Documents:**

<a href="#">3D Model (PDF)</a>	<a href="#">Product Specification TS-48406-001-001 (PDF)</a>
<a href="#">3D Model</a>	<a href="#">Packaging Specification PK-48406-001-001 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Product Specification PS-48406-001-001 (PDF)</a>	



**General**

Product Family	I/O Connectors
Series	48406
Application	Wire-to-Board
Component Type	Receptacle
Overview	<u>USB Connectors: USB Type-A, USB Type-B, and USB Type-C Plugs and Receptacles</u>
Product Name	USB
Standard	USB 3.0
Taxonomy	I/O Connectors
Type	A
UPC	887191519166

**Physical**

Circuits (Loaded)	18
Circuits (maximum)	18
Color - Resin	Blue
Durability (mating cycles max)	5000
Gender	Female
Keying to Mating Part	Yes
Lock to Mating Part	No
Material - Metal	Copper Alloy
Material - Plating Mating	Nickel, Tin
Material - Plating Termination	Gold
Material - Resin	High Temperature Thermoplastic
Mounting Style	Top-Mount
Net Weight	5.450/g
Number of Rows	4
Orientation	Right Angle
PC Tail Length	2.67mm
PCB Locator	Yes
PCB Retention	Yes
Packaging Type	Tray
Panel Mount	No
Pitch - Mating Interface	2.00mm, 2.50mm
Pitch - Termination Interface	2.00mm, 2.50mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Ports	2
Temperature Range - Operating	-20° to +85°C
Termination Interface: Style	Through Hole
Waterproof / Dustproof	No

**Electrical**

Current - Maximum per Contact	1.8A
-------------------------------	------

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2022)4187-DC (10  
June 2022)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

48406 Series

**Mates With**

USB 3.0 Type A Plug

Grounding to Panel  
Voltage - Maximum

Yes  
30V AC/DC

**Material Info**

**Reference - Drawing Numbers**

Packaging Specification  
Product Specification  
Sales Drawing

PK-48406-001-001  
PS-48406-001-001, TS-48406-001-001  
SD-48406-001-001

This document was generated on 12/05/2022

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**