

OBIC0100-24VDC



OBIC0100-24VDC Optocoupler R600 A1-A2=24VDC,4.5-58VDC/1 mA-100 mA,Transistor

General Information

Extended Product Type	OBIC0100-24VDC
Product ID	1SNA645021R2600
EAN	4013614507892
Catalog Description	OBIC0100-24VDC Optocoupler R600 A1-A2=24VDC,4.5-58VDC/1 mA-100 mA,Transistor
Long Description	Screw optocoupler OBIC0100-24VDC: 24VDC Rated control supply voltage/ solid-state output rated 4.5-58VDC, 1 mA up to 100 mA with integrated LED

Ordering

Minimum Order Quantity	10 piece
Customs Tariff Number	85369095

Popular Downloads

Data Sheet, Technical Information	1SVC117001D0200
Instructions and Manuals	1SVC645000M9000

Dimensions

Product Net Width	6 mm
Product Net Height	67.5 mm
Product Net Depth / Length	70 mm
Product Net Weight	0.02 kg

Technical

Function	Boxed optocoupler R600
Output	solid-state output
Output Signal	4.5 ... 58VDC / 1 mA ... 100 mA
Rated Control Supply Voltage (U_s)	24 V DC
Terminal Type	Screw Terminals

Environmental

RoHS Status	Following EU Directive 2011/65/EU
-------------	-----------------------------------

Certificates and Declarations (Document Number)

CCC Certificate	CCC_2017010303938926
CSA Certificate	CSA_254821
cUR Certificate	cUR_E352056
Declaration of Conformity - CE	1SVD982016-0001
EAC Certificate	EAC_RU_C-FR.ME77.B.01634
Instructions and Manuals	1SVC645000M9000
LR Certificate	LR_16_20068
RoHS Information	1SVD982016-0001
UR Certificate	UR_E352056

Container Information

Package Level 1 Units	10 piece
Package Level 1 Width	73 mm
Package Level 1 Height	71 mm
Package Level 1 Depth / Length	80 mm
Package Level 1 Gross Weight	0.23 kg
Package Level 1 EAN	3472596450212

Classifications

Object Classification Code	K
ETIM 4	EC001504 - Optocoupler
ETIM 5	EC001504 - Optocoupler
ETIM 6	EC001504 - Optocoupler
ETIM 7	EC001504 - Optocoupler
eClass	7.0 27371604
E-Number (Sweden)	4029163

Categories

Low Voltage Products and Systems → Control Products → Electronic Relays and Controls → Interface Relays and Optocouplers

