


Copying of this document, and giving it others and the use or communication of the contents thereof, are forbidden without express authority. Offenders are liable to the payment of damages. All rights are reserved in the event of the grant of a patent or the registration of a utility model or design.

Schutzmerkmale nach DIN ISO 15846 beachten!
 Refer to protection notice DIN ISO 15846.



Oberfläche: galvanisch glanzverzinkt, blau chromatiert, Schichtdicke 8-10µm
 alternativ: vernickelt, Schichtdicke 3µm
 Achtung! dekoratives Teil!
 surface: bright zincked, blue chromated, layer thickness 8-10µm
 alternative: nickel-pated, layer thickness 3µm
 Attention! Decorative part!

FR	V5R19	PAPST	Werkstoff / Material: Stahldraht / steel wire DIN EN 10016-1	Volumen / Volume (cm³): 15.272,139		
SAP-Status/State	Änd.-Nr. / Change-No.	CATIA-System-Version/ CATIA-System-Version	CAD-Umgebung/ CAD-Environment	Gewicht / Mass (g): 109,806		
Tolerierung / Tolerances: DIN 7167 Allgmeintoleranzen / Gen. Tolerances: DIN ISO 2768-mK-E	Datum		Artikel / Title:			
	Bearb. / Drawn	20.04.2010	KIENINGER	LZ22 Schutzgitter/guard grille according to DIN EN ISO 13857		
	Gepr. / Checked	23.06.2010	KIENINGER			
Freig. / Released	23.06.2010	SEIDLER				
ebmpapst		Zug.-Nr. / Drawing No: 9920022000		Ers.f.Zchg. / Replaces:		
ebm-papst St. Georgen GmbH & Co KG		Dokumenttyp / Type of Document	Teilnummer (Blatt/Page)	Index / Index	Format / Size:	Maßstab/Scale
		C2D	001	-	A2	1:1