

PCLN clamp holder, negative, right

For face and longitudinal turning with CN indexable insert

ATORN[®]

Application


For longitudinal and face turning with CN indexable insert, 80°

Version

- Precision-manufactured steel support, burnished, hardened, toggle-joint clamping system, type C, working angle 95°, tip angle 80°, clearance angle 0°

Advantage

- Universal use for face and longitudinal turning with large feed depths and unfavourable conditions
- Negative geometry of the body ensures good stability and force absorption at large cutting depths
- Broad range of use: suitable for both finishing and roughing operations



Art. No.	17837 057
ISO name	PCLN R/L 4040 S19
Shaft height	40 mm
Shank width	40 mm
Length	250 mm
Length of head	45 mm
Programming size	50 mm
Suitable for indexable inserts	CN.. 1906..
Tool design	Right
DIN	4983

EAN-Code

4050293347890