

## Digital multimeter

Model testo 760-1



### Application:

For simple and safe measurement of important electrical parameters. Measured variables are automatically detected on the basis of the socket assignment. This eliminates dangerous misconfiguration.

### Version:

- Large, illuminated LCD display

### Advantage:

- Simple and safe operation thanks to automatic measured variable detection
- Convenient one-handed operation by means of function keys

### Delivery:

Multimeter including 2x AAA batteries, 1 set of measuring leads (75024478) and operating instructions.



<b>Art. no.</b>	<b>75024 520</b>
<b>Model</b>	testo 760-1
<b>Min./max. alternating current of measuring range</b>	1 mA-10 A
<b>Min./max. direct current of measuring range</b>	1 mA-10 A
<b>Continuity testing</b>	Yes
<b>Min./max. electrical-resistance measuring range</b>	0.1 MOhm-40 MOhm
<b>Min./max. frequency</b>	0.000001 / 512 kHz
<b>IP protection class</b>	IP 64
<b>Overvoltage protection category</b>	CAT III/600 V, CAT IV/300 V
<b>Length x width x height</b>	167 x 84 x 45 mm
<b>EN standard</b>	61326-1

### EAN-Code

4029547013942