

Base Plates • suitable on pallets DIN 55 201
1103.300



Product Description

Material


- Steel, hardened, ground

More information

Notes

Customized design on request.

Drawing




* These tolerances are valid only for optional exterior stop type.
Slot spacing 70 ± 0,01.


Order information



System	Dimensions							For screws	y	Number of T-slots		Art. No.
	a ₁ x a ₂	c	d	l ₁ ±0.013	l ₂	l ₃	l ₄					
V70	400 x 500	50	20	150	60/40	200	100	M12	12	5 x 7	69	1103.300


Application example











Compliance

RoHS-compliant

Compliant with Directive 2011/65/EU [RoHS].

Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 25.06.2025.

SCIP-code

N/A

Contains Proposition 65 substances



Nickel can cause cancer from exposure.

<https://www.P65Warnings.ca.gov/>

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.

POP-compliant

Contains no persistent organic pollutants – Stockholm Convention [POP] as of September 2025.

PFAS-compliant

Contains no per- and polyfluoroalkyl substances (PFAS).

TSCA-compliant

Agent concentration in this product does not exceed the specified threshold.