

Electronic dial gauge

ID-B

Mitutoyo

Application:

For measuring, e.g. in devices on production machines

Execution:

- Preset function
- ON/OFF
- Reverse piston
- LCD digit size 6.2 mm
- Digimatic
- IP66
- ABSOLUTE system for reliable measurement

Advantage:

- Narrow construction, ideal for multiple point measurements
- Flexible installation due to switchable orientation of display



Art. no.	32019 253
Brand	MITUTOYO
Manufacturer Part Number	543-580
Length measuring range	5.08 mm
Digit increment	0.01 mm
Min./max. measurement force	0-2 N
Error limit	0.02 mm
Data transmission type	DIGIMATIC
IP protection class	IP 66
Functions	ABS function, On/Off, Preset function, Reversal of counting direction
Absolute function	Yes
Automatic switch-off	No
Dynamic measurement	No
Preset function	Yes
Shank diameter	8 mm
Tolerance value entry	No
Manual tolerance markers	No
Number of rechargeable batteries/batteries	1 PCS
Colour reading classification	No
Rechargeable battery/battery capacity	155 mAh
Battery voltage	1.55 V
Weight of rechargeable battery/battery	0.002 kg
Battery designation	1,5 V SR44
Rotating housing	No
Combined indicator for figure/scale reading	No
Reversible counting direction	Yes
Digit height	6 mm
Design	Metric
Display	Digital
Calibration Group Description	Dial gauge
Calibration Group	CE
Gross Weight	0.227 kg
Product Group	3MA

EAN

4946368554228