



SIMATIC S7-400, POWERSUPPLY PS 405: 4A, 24/48/60V DC, 5V DC/4A, ATEXAPPROBATIONIDENTIFICATION

Figure similar

Supply voltage

Rated value (DC)	
<ul style="list-style-type: none"> • 24 V DC • 48 V DC • 60 V DC 	<p>Yes</p> <p>Yes</p> <p>Yes</p>
permissible range, lower limit (DC)	19.2 V; Dynamic 18.5 V
permissible range, upper limit (DC)	72 V; dynamic 75.5 V

Mains buffering

<ul style="list-style-type: none"> • Mains/voltage failure stored energy time • Mains buffering according to NAMUR recommendation 	<p>20 ms</p> <p>Yes</p>
---	-------------------------

Input current

Rated value at 24 V DC	2 A
Rated value at 48 V DC	1 000 mA
Rated value at 60 V DC	800 mA
Inrush current, max.	18 A; Full width at half maximum 20 ms

Output voltage

Type of output voltage	DC
Rated value (DC)	
<ul style="list-style-type: none"> • 5 V DC • 24 V DC 	<p>Yes</p> <p>Yes</p>

Output current

for backplane bus (5 V DC), max.	4 A; no base load required
for backplane bus (24 V DC), max.	0.5 A; idling-proof

short-circuit protection	Yes
Power	
Power consumption, typ.	48 W
Power losses	
Power loss, typ.	16 W
Battery	
Backup battery	
<ul style="list-style-type: none"> • Backup battery — Backup battery (optional) 	Yes; 1 x lithium AA; 3.6 V/2.3 Ah
Hardware configuration	
Slots	
<ul style="list-style-type: none"> • Required slots 	1
Galvanic isolation	
primary/secondary	Yes
Degree and class of protection	
Protection class	1; with protective conductor
Standards, approvals, certificates	
FM approval	Yes; Ta: 0 °C to 60 °C T4
Connection method	
Connecting cables/cross sections	3x 1.5 mm ² , solid or stranded wire with end sleeve, external diameter 3 mm to 9 mm
Dimensions	
Width	25 mm
Height	290 mm
Depth	217 mm
Weights	
Weight, approx.	760 g
last modified:	12.03.2015