

## Cordless combination hammer drill

CHE 18.0-EC

FLEX

### Execution:

- Brushless motor with higher efficiency and longer service life
- Function switch with four functions: drilling, hammer drilling, chiselling, chisel adjustment
- Electronic Management System (EMS) protects the machine, prolongs its life and increases efficiency
- Rotation stop for chipping
- Robust high-pressure die-cast aluminium gear housing
- With throttle switch and continuous operation function
- Electronic rapid acting brake
- Twist-proof additional handle with depth stop
- Integrated LED light with after-glow function
- LED battery capacity display



<b>Art. no.</b>	<b>71030 104</b>
<b>Brand</b>	FLEX
<b>Manufacturer Part Number</b>	461768
<b>Model</b>	CHE 18.0-EC
<b>Manufacturer Article Number</b>	461768
<b>Battery voltage</b>	18 V
<b>Battery included</b>	Yes
<b>Type of rechargeable battery/battery</b>	Li-Ion
<b>Rechargeable battery/battery capacity</b>	5 Ah
<b>Number of rechargeable batteries/batteries</b>	2 PCS
<b>Max. drilling diameter in wood</b>	20 mm
<b>Max. drilling diameter in steel</b>	13 mm
<b>Min./max. idle speed</b>	0-1400 rpm
<b>Min./max. idle impact rate</b>	0-4500 rpm
<b>Suitable for tool holding device</b>	SDS-plus
<b>Length x width x height</b>	280 x 75 x 220 mm
<b>Included in delivery</b>	Handle, depth stop, 2x 5 AH batteries, quick charger, transport case, case insert
<b>Max. drilling diameter in concrete</b>	18 mm
<b>Gross Weight</b>	6.700 kg
<b>Product Group</b>	707

### EAN

4030293230675