

E11508





Wirable socket

SDOGH040MSSFKPG

discontinued article

Alternative article: EVC810 When selecting an alternative article and accessories please note that technical data may differ! –
When selecting an alternative article and accessories please note that technical data may differ! – Discontinuation date: 31.03.2021



Application		
Special feature		Free from silicone; Gold-plated contacts
Free from silicone		yes
Electrical data		
Operating voltage	[V]	< 45 AC / < 70 DC
Max. current load total	[A]	4; (...40 °C)
Operating conditions		
Ambient temperature	[°C]	-25...85
Protection		IP 68
Mechanical data		
Weight	[g]	28.1
Dimensions	[mm]	18 x 18 x 46
Materials		PA
Material nut		brass, nickel-plated
Remarks		
Pack quantity		1 pcs.

E11508



Wirable socket

SDOGH040MSSFKPG

Electrical connection


screw terminals: ...0.75 mm²; Cable sheath: Ø 4...6 mm

Electrical connection - socket

Connector: 1 x M12, straight; Moulded body: PA; Locking: brass, nickel-plated; Contacts: gold-plated



Connection



discontinued article

Alternative article: EVC810 When selecting an alternative article and accessories please note that technical data may differ! –
When selecting an alternative article and accessories please note that technical data may differ! – Discontinuation date: 31.03.2021