

TECHNICAL DATASHEET


Update : 25/02/2019

CONICAL CARBIDE MILLING BIT POINTED HEAD - FORM M



Description

For use, please refer to the table on page 109



Characteristics

Ref.	EAN	Tail diameter mm	Shape of head	Total length	Teeth	Head diameter	Scope	Capacity length mm
847253	3660338086120	3	Model M	38	Crossed	3	Universal	11
847254	3660338086137	6	Model M	50	Crossed	6	Universal	19
847255	3660338086144	6	Model M	65	Crossed	9,5	Universal	16
847256	3660338086151	6	Model M	70	Crossed	12,7	Universal	25
863244	3660338178498	3	Model M	45	Crossed	6	Universal	13
863245	3660338178504	6	Model M	73	Crossed	16	Universal	25
863246	3660338178511	3	Model M	38	Simple	3	Finish	11
863247	3660338178528	3	Model M	45	Simple	6	Finish	13
863248	3660338178535	6	Model M	50	Simple	6	Finish	19
863249	3660338178542	6	Model M	65	Simple	9,5	Finish	16
863250	3660338178559	6	Model M	70	Simple	12,7	Finish	25