


TYPE 1



NOTES:

1. MATERIAL: NYLON 4/6 HEAT STABILIZED.
2. COLOR: NATURAL (OLIVE)
3. TYPE I OPERATING TEMPERATURE RANGE: -40°F/-40°C TO 302°F/150°C
TYPE II OPERATING TEMPERATURE RANGE: -40°F/-40°C TO 266°F/130°C
4. FLAMMABILITY: UL94 V-2
5. MINIMUM INSTALLATION TEMPERATURE: 0°F/-18°C
6. COMPLIES WITH IEC 62275, EN62275 AND NMX-J-623-ANCE, TYPE I

CAT. NO.	A	B	C	D	E	F	MIN TENSILE RATING LBS/[N]	MIN WIRE BUNDLE	MAX. WIRE BUNDLE	PKG QTY	TOOL/SETTING
TYHT23M	3.62 [91.9]	.092 [2.34]	.036 [0.91]	.130 [3.30]	.185 [4.70]	.153 [3.88]	18/80	.062 [1.57]	.787 [20.0]	1,000	ERG50/1-3 OR WT199/1-3 (MS90387-1)
TYHT24M	5.5 [139.7]	.140 [3.55]	.045 [1.14]	.156 [3.96]	.250 [6.35]	.180 [4.57]	40/178	.062 [1.57]	1.14 [29.0]	1,000	ERG50/3-5 OR WT199/3-5 (MS90387-1)
TYHT25M	7.31 [186]	.188 [4.77]	.048 [1.22]	.250 [6.35]	.315 [8.00]	.220 [5.89]	50/222	.187 [4.75]	1.77 [45.0]	1,000	ERG50/6-8 OR WT199/6-8 (MS90387-1)
TYHT27M	13.4 [340]	.270 [6.86]	.063 [1.60]	.360 [9.14]	.480 [12.2]	.320 [8.13]	120/534	.187 [4.75]	3.50 [89.0]	500	ERG120/5-8 OR WT197/5-8 (MS90387-2)
TYHT28M	14.2 [361]	.187 [4.75]	.050 [1.27]	.250 [6.35]	.315 [8.00]	.220 [5.89]	50/222	.187 [4.75]	4.00 [102.0]	1,000	ERG50/6-8 OR WT199/6-8 (MS90387-1)

GENERAL NOTES

1. ALL DIMENSIONS ARE FOR REFERENCE ONLY.
2. DIMENSIONS IN BRACKETS [] ARE IN METRIC UNITS.

REVISIONS

- | | |
|---|---|
| 6 | SEE ERN 2013330 FOR APPROVAL SIGNATURES & RELEASE DATE.
PROJECT NO: FM401183 |
|---|---|

Thomas & Betts
www.tnb.com

DESCRIPTION: **TYHT SERIES EXTRA HIGH TEMP TY-RAP CABLE TIES**

ORIGINAL PROJECT NO / (ERN NO) FM401181 / (2005322)	SHEET NO: 1 OF 1	REV. NO: 6	DRAWING NO: WSD-000156
---	----------------------------	----------------------	----------------------------------