

## LOW TRIBOCHARGING STRETCH FILM

85-100-0018 / 0019

### Product specifications

Material:	Low tribocharging polyolefin
Colour:	Pink
Thickness:	23 $\mu$
Width:	500mm
Tensile strength:	MD > 39 N/mm <sup>2</sup> TD > 22 N/mm <sup>2</sup>
Elongation:	MD > 450% TD > 700%
Core diameter:	50mm
Shelf life:	2 years



### ESD safe Properties

Surface resistance:	$\leq 10 \times 10^{12} \Omega$
Decay time:	From 1000V to 100V < 2 seconds
Compliant to:	EN 61340-5-1

### Dimensions

85-100-0018:	Weight = 2.6 kg +/- 5% Core weight: 400g approx Core diameter: 50mm Length = 200m approx – for quantity control take into account only the weight of the film Total diameter: approx 100mm
85-100-0019:	Weight = 13 kg +/- 5% Core weight: 400g approx Core diameter: 75 mm Length = 1000m approx – for quantity control take into account only the weight of the film. Total diameter: approx 190 mm.