

Shoulder milling cutter VSM890™

For indexable milling inserts SN.X 1204..



Application:

The WIDIA™ Victory™ angular milling cutter VSM890™-12 guarantees precise 90-degree shoulders and offers maximum economy with eight effective cutting edges per indexable insert. With an axial cutting depth of up to 8.0 mm, the tool also guarantees high productivity.

Execution:

- Double-sided, robust indexable insert with 8 cutting edges
- Highly positive geometry for lower cutting forces
- Integrated facing chamfer for excellent surface quality
- Internal cooling

Advantage:

- True 90° surfaces
- Enables cutting depths of up to 9.8 mm
- Low burr formation



Art. no.	16044 242
Brand	WIDIA
Manufacturer Part Number	6596124
Cutting edge diameter	160 mm
Length	63 mm
Bore diameter	40 mm
max. ap	9.8 mm
Number of cutting edges	16 PCS
Gross Weight	8.960 kg
Product Group	1XJ

EAN

4061779074056