



5

4

3

2

1





SPECIFICATION


Performance level	PL2
Filter type	C
Capacitance	47pf±20%
Working Voltage	100v
Current Rating	7,5A
Insulation Resistance	>1GΩ

Solder buckets for AWG 20 Max

FREQUENCY (MHz)	ATTENUATION dB
5	-
10	-
50	-
100	-
500	30dB
1000	35dB



Mod.	Dat.	Name	Dat.	Name
			8-JUL-02	CV
			12/01/12	JB
36283	12/01/12	SD		
33250	03/11/05	JMDR		
31058	8-JUL-02	CV		
			HARTING EURL F-95972 Paris	



All Dim. in mm  
Orig. Size DIN A 4

D-Sub, female, straight  
15 Poles, turned solder  
buckets, with holes

Ma?Mstab/  
Scale

1.5:1



TB 09642117210

Blatt/ Page

1 / 1

Sub.

D

C

B

A