

Quick coupling plug KS4-1/2-I

Part number: 531680

FESTO



Data sheet

Feature	Value
Nominal size	7.85 mm
Short type code	KS4
Operating pressure complete temperature range	-0.95 bar ... 12 bar
Standard nominal flow rate	1305 l/min
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance class CRC	1 - Low corrosion stress
Ambient temperature	-10 °C ... 60 °C
Nominal torque	32.5 Nm
Tolerance for nominal tightening torque	± 20%
Product weight	57 g
Pneumatic connection, port 1	Female thread G1/2
Note on materials	RoHS-compliant