

Electronic dial gauge

ID-C with low gauging force

Mitutoyo

Application:

for measuring lengths and differences in length, e.g. concentricity, flatness, position measurements.

Version:

- Preset function
- ON/OFF
- ABSOLUTE system for reliable measurement
- LCD digit size 11 mm
- LOCK function (key lock)
- Digimatic



Art. no.	32019 284
Length measuring range	12.7 mm
Digit increment	0.01 mm
Min./max. measurement force	0.2-0.5 N
Error limit	0.02 mm
Repeat accuracy	0.01 mm
Data transmission type	DIGIMATIC
IP protection class	IP 42
Functions	Absolute function, Preset function, On/Off, Reversal of counting direction
Absolute function	Yes
Automatic switch-off	No
Dynamic measurement	No
Preset function	Yes
Shank diameter	8 mm
Tolerance value entry	No
Manual tolerance markers	No
Calibration Group	CE
Colour reading classification	No
Number of rechargeable batteries/batteries	1 PCS
Battery designation	1,5 V SR44
Rotating housing	Yes
Combined indicator for figure/scale reading	No
Reversible counting direction	Yes
Digit height	11 mm
Design	Metric
Display	Digital
Calibration Group Description	Dial gauge
WEEE (taking back waste electrical and electronic equipment)	5

EAN-Code

4946368586649