

VERLÄNGERUNGEN EXTENSIONS



VL1-Ø19/15/M14x1/4-20UNC-A



VL1-Ø20/75/M14I-A



VL1-Ø19/15/M14x1/4-20UNC-A



VL2-Ø15/100/M14I-A



VL1-Ø25/20/M14x1/4-20UNC-A



VL1-Ø30/15/M10x1,25A-I



VL1-Ø30/20/M10x1,25A-I



VL2-Ø21/25/M10x1,25A-I

Aluminium

Für Werkzeug For Tool	Typ Type	Gewinde maschinenseitig Thread Machine Side	Gewinde tellerseitig Thread Plate Side	Abmessungen Dimensions	Artikel-Nr. Item No.
GW 13/7 GW 13/310 GW 30/341 GW 30/342	VL1-Ø25/20/M14IxM6A	M14 - IG	M6 - AG	Ø 25 x 20 mm	19000002
	VL1-Ø19/15/M14Ix1/4-20UNC-A		1/4"-20 UNC - AG	Ø 19 x 15 mm	19000006
	VL1-Ø25/20/M14Ix1/4-20UNC-A		1/4"-20 UNC - AG	Ø 25 x 20 mm	19000003
	VL1-Ø20/30/M14I-A		M14 - AG	Ø 20 x 30 mm	19000007
	VL1-Ø20/75/M14I-A		M14 - AG	Ø 20 x 75 mm	19000004
	VL1-Ø20/85/M14I-A		M14 - AG	Ø 20 x 85 mm	19000008
	VL2-Ø15/100/M14I-A		M14 - AG	Ø 15 x 100 mm	19000005
GEV 30	VL1-Ø30/15/M10x1,25A-I	M10 x 1,25 - AG	M10 x 1,25 - IG	Ø 30 x 15 mm	19000011
	VL1-Ø30/20/M10x1,25A-I		M10 x 1,25 - IG	Ø 30 x 20 mm	19000012
	VL2-Ø21/25/M10x1,25A-I		M10 x 1,25 - IG	Ø 21 x 25 mm	19000013
	VL2-Ø14/10/M10x1,25Ax1/4-20UNC		1/4"-20 UNC - AG	Ø 14 x 10 mm	19000014

AG – Außengewinde/Male thread

IG – Innengewinde/Female thread

1/4"-20 UNC für die Verwendung des Roloc™-Systems/for usage of Roloc™-system

