

## Ratchet cable cutters

For diameters up to 32 or 52 mm, with 2-component grip covers



### Application:


For cutting copper and aluminium cables.

### Execution:

- Special-grade tool steel, oil-hardened
- Hardened, precision-ground blades
- Not suitable for steel wire and piano wire

### Advantage:

- Cut smoothly and cleanly without crushing
- One-handed operation using ratchet principle, low force required thanks to optimum transmission ratios
- 2-speed gear ring drive for simple cutting
- Simple to use thanks to low weight and compact design; even possible to use in confined spaces
- With pinching guard to prevent crushing injuries



<b>Art. no.</b>	<b>53102 010</b>
<b>Brand</b>	KNIPEX
<b>Manufacturer Part Number</b>	95 31 250
<b>Length</b>	250 mm
<b>Max. medium wire diameter cutting capacity</b>	32 mm
<b>Material of handle</b>	2-component plastic
<b>Gross Weight</b>	0.688 kg
<b>Product Group</b>	535

### EAN

4003773043935