## GS1DU3

TeSys GS, disconnect switch, fuse, 3 P, 600 V, UL 30 A, Type J fuse





#### Main Range TeSys Product name TeSys GS GS1D Device short name Product or component Switch-disconnector-fuse type Device application Protection Design Compact Poles description 3P Protected poles 3t description 3 NO Contacts type and composition [Ith] conventional free 30 A 104 °F (40 °C) air thermal current [le] rated operational 30 A current Fuse type UL

J

AC DC 50/60 Hz

#### Complementary

Type of operating handle	External frontal	
Mounting support	Plate Rail	
[Ui] rated insulation voltage	690 V	
[Uimp] rated impulse withstand voltage	8 kV	
Rated operational power in W	15 KW 400 V 18.5 KW 500 V 25 kW 690 V	
Short-circuit withstand	5.5 kA	
Mechanical durability	10000 cycles	
Electrical durability	6000 cycles	
Connections - terminals	Power circuit lugs-ring terminals 0.000.01 in² (26 mm²)	
Tightening torque	Power circuit 26.55 lbf.in (3 N.m)	

Fuse size

Network type

Network frequency

#### **Environment**

Standards	CSA C22.2 No 4 UL98	
Product certifications	LOVAG LROS (Lloyds register of shipping) ASEFA	
IP degree of protection	IP20 IEC 60529 with terminal cover)	
Ambient air temperature for operation	-4158 °F (-2070 °C)	
Ambient air temperature for storage	-40176 °F (-4080 °C)	
Fire resistance	1760 °F (960 °C) body IEC 60695-2-1	
Height	4.57 in (116 mm)	
Maximum Width	4.13 in (105 mm)	

Depth	3.90 in (99 mm)
Net Weight	1.54 lb(US) (0.7 kg)

## Ordering and shipping details

Category	22640 - IEC DISCONNECT-GS1,LK3
Discount Schedule	l11
GTIN	00785901367529
Nbr. of units in pkg.	1
Package weight(Lbs)	1.42 lb(US) (0.64 kg)
Returnability	Yes
Country of origin	FR

# Packing Units

Unit Type of Package 1	PCE
Package 1 Height	4.96 in (12.6 cm)
Package 1 width	5.35 in (13.6 cm)
Package 1 Length	6.18 in (15.7 cm)
Unit Type of Package 2	S03
Number of Units in Package 2	8
Package 2 Weight	12.54 lb(US) (5.688 kg)
Package 2 Height	11.81 in (30 cm)
Package 2 width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)
Unit Type of Package 3	P06
Number of Units in Package 3	32
Package 3 Weight	70.81 lb(US) (32.12 kg)
Package 3 Height	30.31 in (77 cm)
Package 3 width	31.50 in (80 cm)
Package 3 Length	23.62 in (60 cm)

#### Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Styrene, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
REACh Regulation	REACh Declaration
REACh free of SVHC	Yes
EU RoHS Directive	Compliant EEU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	₫Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	☑ End Of Life Information

## Contractual warranty

Warranty	18 months