

T-slot bolts



Application:

For clamping workpieces on machine tables.

Execution:

- Tempered
- Rolled thread
- Forged
- With milled groove guide
- M8 to M12, strength class 10.9
- M16 to M24, strength class 8.8
- DIN 787



Art. no.	26200 420
Brand	AMF
Manufacturer Part Number	80895
DIN	787
Thread dimension	M12
Groove width	14 mm
Length excluding head	50 mm
Outer diameter	13.7 mm
Thread length	35 mm
Length of head	22 mm
Head height	8 mm
Gross Weight	0.123 kg
Product Group	260

EAN

402077208089 1