

2-axle flat-bed hand truck

Open, carrying capacity 700 to 1250 kg

Version:

- Module system
- From welded profiled steel, 4 tubular sleeves at corners
- Scissors-shaped drawbar with safety handle with soft rubber grip and with an automatic damped retraction in resting position
- Loading area covered with slip-resistant phenolic resin coated waterproof plywood
- Wheels either with solid rubber or air tyres, hubs with roller bearings
- Automatic parking brake acting on the front wheels, according to EN 1757-3
- Powder coating: RAL 5007, brilliant blue, durable surface protection, impact and scratch-resistant



Art. no.	50267 831
Design	Open
Material of loading surface	Wood
Length	1545 mm
Height	1130 mm
Loading surface length	1200 mm
Width	800 mm
Loading-surface width	800 mm
Loading surface size	1200 x 800 mm
Load-carrying capacity	700 kg
Colour	Brilliant blue RAL 5007
With wheel lock	Yes
Total stop optional	No
Wheel width	85 mm
Wheel diameter	260 mm
Material of wheel	Air
Surface	Powder-coated

EAN-Code

4017976014029