




**MIRO 6.2 24VDC-1U OUTPUT RELAY**

IN: 24 VAC/DC - OUT: 250 VAC/DC / 6 A

1 NO/NC contact  
24 V AC/DC  
Spring clamp terminals

[Link to Product](#)**Illustration**

stay connected



Product may differ from Image

### Approvals



### Input

Connection voltage - current	24 V DC (19.2...30 V DC) - 17 mA
LED display	LED (green)

### General data

Mech./ elect. life	20.000.000 switching cycles/load dependent
Test isolation voltage	4 kV; safe separation (EN 60947-1)
Mounting method	DIN-rail mountable (EN 60715)
Temperature range	-20...+55 °C
Dimensions H × W × D	90×6.2×65 mm

### Output

Switching voltage	max. 250 V AC/DC
Switching current per output	max. 6 A
Min. load current	100 mA (12 V DC)
Power rating (voltage dependent)	max. 1500 VA/120 W
Switching frequency	max. 10 Hz

Contact material	Ag Sn O2
Energize/release/contact bounce time	10/15/1.5 ms

**Commercial data**

country of origin	CZ
customs tariff number	85364900
minimum order quantity	1