

Drill/countersink milling cutter, 90°, with Weldon shank

For indexable milling inserts AP.. 1003..

ATORN[®]

Application


For drilling/countersinking in all materials.

Version

- With Weldon shank
- Wear-resistant, nickel-plated version
- Robust supports
- Clamping screw tightening torque (indexable insert) M2.5 = 1.2 Nm

Advantage

- High cutting performance
- Safe chip removal thanks to positive cutting geometry



Art. No.	16035 054
Cutting edge diameter	20 mm
Clearance length	30 mm
Length	180 mm
Shaft diameter	20 mm
max. ap	17 mm
Number of cutting edges	2 PCS
Number of cutting inserts	3 PCS
Suitable indexable insert no.	21

EAN-Code

4050293539776

