

MC2535adwe













## Lexmark MC2535adwe

The multifunction Lexmark MC2535adwe builds on print speed up to 33 pages per minute\* with a 10.9 cm colour touch screen. In addition to reliably handing diverse media types and sizes, it includes built-in Wi-Fi and tools that help you both minimise toner consumption and get the colour right.



# Ready when you are

- 1.2-GHz quad-core processor and up to 6 GB memory drives printing at up to 33 ppm.\*
- Scan at up to 47 pages per minute.
- Steel frame and durable design stands up to heavy use and harsh environments.
- ▶ Long-life fuser and imaging components extend uptime.
- Unison<sup>™</sup> Toner replacement cartridges deliver up to 3500 colour and 8000 monochrome pages\*\*.
- ▶ Keep printing in black even when colour toner is empty.

# Colour that keeps saving

- PANTONE® calibration, embedded colour sample pages and Lexmark Colour Replacement produce accurate, professional colour output in-house.
- Save toner with suite of tools that let you choose when and how much colour to print.

#### Input that works

- Reliable, flexible media handling supports cardstock, small media, and envelopes from the main tray or a convenient single-sheet feeder.
- > 251 pages of standard input can grow to 1451.

#### Interact with ease

- Tiltable 10.9 cm e-Task touch screen comes with convenience and productivity apps and is customisable to meet your needs.
- Front USB port allows walk-up printing from popular file formats without a computer.
- Compact footprint allows flexible placement in more locations.
- Connect easily via Ethernet, USB, Wi-Fi or simple mobile printing options.

### **Full-spectrum security**

- Lexmark's full-spectrum security architecture helps keep your information safe—in the document, on the device and over the network.
- Keypoint Intelligence Buyers Lab honoured Lexmark with a prestigious BLI PaceSetter award for Document Imaging Security\*\*\*.



### **Built for planet earth**

- Energy management features reduce power consumption in active use or sleep mode.
- Standard two-sided printing saves paper.
- Recycle cartridges through the award-winning Lexmark Cartridge Collection Programme (LCCP).

## Lexmark MC2535adwe



- 1 MC2535adwe with 10.9 cm e-Task colour touch screen 462 x 442 x 588 mm
- 2 650-sheet duo tray 133 x 424 x 416 mm
- 3 550-sheet tray 133 x 424 x 416 mm

Adjustable printer stand (not shown) 521 x 653 x 625 mm

Swivel cabinet (not shown) 263 x 476 x 600 mm

Standard
Optional

Note 1: Supports one optional 650-sheet duo tray; or one optional 650-sheet duo tray and one optional 550-sheet tray with the 650-sheet duo tray on top.

Note 2: All measurements are shown as height x width x depth. For more information about supported configurations, refer to the Printer, Option and Stand Compatibility Guide at http://www.lexmark.com/publications/furniture\_safety/

### © 2018 Lexmark. All rights reserved.

Lexmark, the Lexmark logo and Unison are trademarks of Lexmark International, Inc., registered in the United States and/or other countries. AirPrint and the AirPrint Logo are trademarks of Apple, Inc. Google Cloud Print is a trademark of Google, Inc. MOPRIA®, the Mopria® Logo™ and the Mopria® Alliance logos are trademarks, service marks, and certification marks of Mopria Alliance, Inc. in the United States and other countries. PANTONE®, PANTONE® Goe™ and other Pantone, Inc. trademarks are property of Pantone, Inc. All other trademarks are the property of their respective owners.

 $This \ product \ includes \ software \ developed \ by \ the \ OpenSSL \ Project \ for \ use \ in \ the \ OpenSSL \ Toolkit \ (http:// \ ww.openssl.org/).$ 



Product specifications	Lexmark MC2535adwe
Print	
Display	Lexmark e-Task 4.3-inch (10.9 cm) colour touch screen
Print Speed: Up to⁵	Black: 33 ppm / Colour: 33 ppm
Time to First Page: As fast as	Black: <8.5 seconds / Colour: <8.5 seconds
Print Resolution	Black: 1200 x 1200 dpi, 4800 Color Quality (2400 x 600 dpi) / Colour: 1200 x 1200 dpi, 4800 Color Quality (2400 x 600 dpi)
Memory / Processor	Standard: 2048 MB / Maximum: 6144 MB / Quad Core, 1200 w/ GPU MHz
Hard Disk	Option available
Recommended Monthly Page Volume <sup>1</sup>	1500 - 8500 pages
Maximum Monthly Duty Cycle: Up to <sup>2</sup>	85000 pages per month
Сору	
Copy Speed: Up to <sup>5</sup>	Black: 33 cpm / Colour: 33 cpm
Time to First Copy: as fast as	Black: 9 seconds / Colour: 9.5 seconds
Scan	
Scanner Type / ADF Scan	Flatbed scanner with ADF / RADF (reversing Duplex)
A4/Ltr Duplex Scan Speed: Up to	Black: 21 / 23 sides per minute / Colour: 13 / 14 sides per minute
A4/Ltr Simplex Scan Speed: Up to	Black: 47 / 50 sides per minute / Colour: 30 / 32 sides per minute
ADF Paper Input Capacity: Up to	50 pages 75 gsm bond
Fax	
Modem Speed	Max is 33,600 bps, V.34 Half-Duplex Kbps
Supplies <sup>6</sup>	
Laser Cartridge Yields (up to)	1,000-page Black and Colour (CMYK) Cartridges, 6,000-page Black Extra High Yield Cartridge, Average continuous cartridge yield is stated number of standard pages as listed. Declared yield value in accordance with ISO/IEC 19798., 2,300-page Colour (CMY) High Yield Cartridges, 3,000-page Black High Yield Cartridge, 3,500-page Colour (CMY) Extra High Yield Cartridge, 8,000-page Black Ultra High Yield Cartridge
Photoconductor Estimated Yield: Up to <sup>4</sup>	125000 pages, based on 3 average letter/A4-size pages per print job and ~ 5% coverage
Cartridge(s) Shipping with Product	1,400-page Colour (CMY) Starter Return Program Toner Cartridge, 3,000-page Black Starter Return Program Toner Cartridge
Paper Handling	
Included Paper Handling	250-Sheet Input, 150-Sheet Output Bin, Integrated Duplex, Single-Sheet Manual Feed
Optional Paper Handling	550-Sheet Tray, 650-Sheet Duo Tray
Paper Input Capacity: Up to	Standard: 250+1 pages 75 gsm bond / Maximum: 1450+1 pages 75 gsm bond
Paper Output Capacity: Up to	Standard: 150 pages 75 gsm bond / Maximum: 150 pages 75 gsm bond
Media Types Supported	Card Stock, Paper Labels, Plain Paper, Vinyl Labels, Refer to the Card Stock & Label Guide.
Media Sizes Supported	10 Envelope, 7 3/4 Envelope, A4, A5, B5 Envelope, C5 Envelope, DL Envelope, Hagaki Card, Executive, Folio, JIS-B5, Lega Letter, Universal, Oficio, A6
General Information <sup>3</sup>	
Standard Connectivity	USB 2.0 Specification Hi-Speed Certified (Type B), Gigabit Ethernet (10/100/1000), 802.11b/g/n Wireless, Front USB 2.0 Specification Hi-Speed Certified port (Type A)
Optional Network Ports	Marknet N8372 WiFi Option
Noise Level: Operating	Print: 52 dBA / Copy: 56 dBA / Scan: 55 dBA
Specified Operating Environment	Humidity: 8 to 80% Relative Humidity, Altitude: 0 - 3048 Meters (10,000 Feet), Temperature: 10 to 32°C (50 to 90°F)
Product Guarantee	4-year guarantee (upon registration)
Size (mm - H x W x D) / Weight	462 x 442 x 588 mm / 27.1 kg

All information in this brochure is subject to change without notice. Lexmark is not liable for any errors or omissions.

<sup>&</sup>lt;sup>1</sup>"Recommended Monthly Page Volume" is a range of pages that helps customers evaluate Lexmark's product offerings based on the average number of pages customers plan to print on the device each month. Lexmark recommends that the number of pages per month be within the stated range for optimum device performance, based on factors including: supplies replacement intervals, paper loading intervals, speed, and typical customer usage. <sup>2</sup>"Maximum Monthly Duty Cycle" is defined as the maximum number of pages a device could deliver in a month using a multishift operation. This metric provides a comparison of robustness in relation to other Lexmark printers and MFPs. <sup>3</sup>Printers are sold subject to certain license/agreement conditions. See www.lexmark.com/printerlicense for details. <sup>4</sup>Actual Yield may vary based on other factors such as device speed, paper size and feed orientation, toner coverage, tray source, percentage of black-only printing and average print job complexity. <sup>5</sup>Print and copy speeds measured in accordance with ISO/IEC 24734 and ISO/IEC 24735 respectively (ESAT). For more information see: www.lexmark.com/ISOspeeds. <sup>6</sup>Product functions only with replacement cartridges designed for use in a specific geographical region. See www.lexmark.com/regions for more details.

