

## Digital inspection camera

micro CA-25™

**RIDGID**

### Application:

For detailed visual inspections at short range.

### Version:

- 2.4" colour LCD display with 480 x 234 pixel resolution
- Aluminium camera head with ultra-bright LED illumination
- Flexible camera cable waterproof to 3 m

### Advantage:

- Live images transmitted to external device via video output
- Digital 180° screen rotation for upright image display

### Delivery:

micro CA-25™, camera head 17 mm with 0.9 m, RCA/cinch cable, attachable tools: mirror, hook and magnet, 4x 1.5 V AA batteries, transport case



|   |                  |
|---|------------------|
| <b>Art. no.</b>                         | <b>41500 025</b> |
| <b>Image rotation</b>                   | 360° (2 x 180°)  |
| <b>Display resolution</b>               | 480 x 234 pix    |
| <b>Model</b>                            | micro CA-25      |
| <b>Field of vision</b>                  | 72 Degree        |
| <b>Screen size</b>                      | 2.4 in           |
| <b>External memory on SD card</b>       | Up to 32 GB      |
| <b>Camera head diameter</b>             | 17 mm            |
| <b>Number of LEDs</b>                   | 4 PCS            |
| <b>Cable length</b>                     | 0.9 m            |
| <b>Camera cable, extending</b>          | No               |
| <b>Speech recording</b>                 | No               |
| <b>Image, video and audio recording</b> | No               |
| <b>Video output</b>                     | PAL              |

### EAN-Code

0095691400437