

Hydraulic jacks

Model AJS and AJH

Yale

Application:

The jacks are universal and are used in all workshops, on construction sites, in the steel industry and in shipyards.

Execution:

- Extremely low-weight aluminium jacks.
- All jacks feature a hardened steel thrust piece and a sensitive drain valve that is operated with the pump lever.
- The 20 - 100 t jacks can be used in vertical and horizontal situations.
- All jacks feature a pressure relief valve.
- 6.5 and 10 t jacks, can be used in all positions (even overhead).

Delivery:

1x YALE aluminium hydraulic jack, model AJS 65 6.5 t, travel 75 mm.



Art. no.	29754 100
Brand	YALE
Model	AJS-104
Compressive force	10.2
Lift height	115 mm
Construction height, retracted	182 mm
Surface area length	171 mm
Surface area width	76 mm
Load-carrying capacity	10.2 t
Weight	6.3 kg
Gross Weight	7.100 kg
Product Group	278