



Technical details

Approvals:	CE;cULus Listed;TÜV;CCC
Application options:	Instantaneous contact expansion
Operating modes:	Single-channel;without detection of shorts across contacts
Standards:	EN 60204-1;EN 62061;EN ISO 13849-1;VDE 0113-1
Supply voltage (V):	24,0
Supply voltage type:	DC
Terminal style:	fixed
Terminal type:	Screw terminal
Number of instantaneous safety contacts:	4
Max. current at DC13 I (6 cycles/min):	5.0 A
Voltage at AC15:	230 V
Width dimension:	22.5 mm
Height dimension:	87.0 mm
Depth dimension:	121.0 mm
Gross weight:	180 g
Net weight:	175 g
Ambient temperature:	-10 - 55 °C