


Non-Return Valves

Material: Housing: Anodised aluminium.
Seals NBR.

Medium: Compressed air, filtered, lubricated or non-lubricated.
Mode of operation: Poppet valve.
Operating pressure: -0.9 to 16 bar.
Operating temperature: 80°C.




Ordering details e.g.: Product No. 865 800 04, Non-Return Valves, Tube Outer-Ø 4 mm

Symbol	Product No.	Ø A mm	C mm	Ø K mm	Flow Operating Pressure 6 bar	Weight g
	865 800 04	4	49	11	0,11 (159.6 l/min)	10
	865 800 06	6	56,5	13	0,44 (659,4 l/min)	16
	865 800 08	8	61	15	0,89 (1344 l/min)	22
	865 800 10	10	77,5	20	1,26 (1890 l/min)	48
	865 800 12	12	88,5	22	1,87 (2814 l/min)	64

Plug with Sealing Ring

Material: Brass, nickel plated. Seal ring from aluminium.



Ordering details e.g.: Product No. 865 900 05, Plug with Sealing Ring, Thread M5

Product No.	A	C mm	G mm	SW mm	Weight g
865 900 05	M5	8	4,5	8	2
865 900 28	G1/4 A	13	9	17	13
865 900 38	G 3/8 A	13,5	9,5	19	20
865 900 48	G1/2 A	14,5	10	24	27
865 900 68	G3/4 A	16	11	30	49
865 900 88	G 1 A	17	12	40	190

Tube Cutter



Ordering details e.g.: Product No. 869 999 00, Tube Cutter

Product No.	Weight g
869 999 99	25

Disconnection Tool



Ordering details e.g.: Product No. 869 999 90, Disconnection Tool

Product No.	Weight g
869 999 90	45