

Beacon LED Wallwash - High Output

BEACON WW LED HO 4K L3 WHT
2059109



Product features

- 2059109 BEACON WW LED HO 4K L3 WHT Integrated LED spotlight, white RAL 9016, compact and minimalist design, ideal for museum, gallery and display applications, die-cast aluminium body, passive cooling heatsink, uniform ceiling to floor vertical illuminance up to 4m height and 4.5m horizontal spread, beam angle: asymmetric wallwash, optics: asymmetric glass lens, colour temperature: 4000K warm white, total system power: 48W, total fixture output: 4916lm, luminaire efficacy: 102lm/W, LOR: 100%, colour rendering: Ra 85 typical, LED Chromacity: 3 step MacAdam ellipse, lifetime: 50,000 hours at 70% of the original output (L70), energy class: A++, A+, A, IR/UV free light source without heat radiation, operating voltage: 220-240V / 50-60Hz, drive current: 1200mA, electronic driver, non-dimmable, switched only, power factor: 0.98, electrical protection: CLASS I, 3-circuit track adaptor, suitable for Concord Lytespan 3 track, ingress protection rating: IP20, suitable for internal environment only, horizontal rotatio...




PRODUCT OVERVIEW

Product name	BEACON WW LED HO 4K L3 WHT
Technology	LED
Housing	Aluminium
Mount	Track mounting
Environment	Internal
General application	Museums & Galleries, Retail
ETIM Class	EC001744
E-number FI	4276819
Warranty	5 years
Fixture luminous flux (lm)	4916
Luminaire efficacy (lm/W)	102
LOR (%)	100
Colour temperature (K)	4000
Light colour	Neutral White
CRI (Ra)	85
Colour Consistency (SDCM)	3
Photobiological Risk Group	RG1
Total power consumption (W)	48
Product Voltage (V)	240
Electrical protection	Class I
Control gear type	Electronic ballast
Dimming method	N/A
Housing colour	White
IP rating	IP20
Product EAN number	5025768591091

PHOTOMETRY

Beacon LED Wallwash - High Output

BEACON WW LED HO 4K L3 WHT
2059109



TECHNICAL DRAWINGS

