


U.I. Lapp GmbH	<b>PRODUCT INFORMATION</b>	
	<b>SKINTOP® CLICK-R</b>	<b>12.09.2012</b>

For the benefits, refer to SKINTOP® CLICK



### Info

The most innovative cable insertion system in the market for a fast and highly flexible assembly. Simply click in - turn to the left - turn to the right - finished. The result: fixed, centred, strain-relieved fitting and maximum protection class in a few seconds.

### Application range

With reducing seal insert, to seal cables with smaller outer diameters.

### Approvals (Norm references)

UL File Nr. E79903

### Included

Included: disassembly tool

### Remark

Photographs are not to scale and do not represent detailed images of the respective products.

### Technical Data


Colour delivered:	Silver grey (RAL 7001) Light grey (RAL 7035) Black (RAL 9005), UV-resistant
Material:	Body: special polyamide Seal: special elastomer
Temperature range:	Dynamic: -20°C to +100°C Fixed: -40°C to +100°C


Product Management	Document: LAPP_PRO26625EN.pdf	1 / 3
--------------------	-------------------------------	-------

**SKINTOP® CLICK-R**

12.09.2012

Part number	Article designation / size	Clamping range ØF (mm)	M (hole in mm)	Thread/ female PG/NPT	SW1/SW2 mm	Overall length/ C (mm)	Thread length inner mm	Wall thickness/ S (mm)
<b>SKINTOP® CLICK-R light grey</b>								
53112925	CLICK-R 12	1 - 5	12.3 (-0.2)		15 / 18	40.0	8.0	1 - 4
53112689	CLICK-R 16	4 - 7	16.3 (-0.2)		19 / 22	42.0	8.0	1 - 4
53112690	CLICK-R 20	5 - 10	20.3 (-0.2)		25 / 27	45,5	8.0	1 - 4
53112691	CLICK-R 25	6 - 13	25.3 (-0.2)		30 / 34	48,5	8.0	1 - 4
53112926	CLICK-R 32	7 - 15	32.3 (-0.2)		36 / 40	55.0	8.0	1 - 4
<b>SKINTOP® CLICK-R silver grey</b>								
53112927	CLICK-R 12	1 - 5	12.3 (-0.2)		15 / 18	40.0	8.0	1 - 4
53112879	CLICK-R 16	4 - 7	16.3 (-0.2)		19 / 22	42.0	8.0	1 - 4
53112880	CLICK-R 20	5 - 10	20.3 (-0.2)		25 / 27	45,5	8.0	1 - 4
53112881	CLICK-R 25	6 - 13	25.3 (-0.2)		30 / 34	48,5	8.0	1 - 4
53112928	CLICK-R 32	7 - 15	32.3 (-0.2)		36 / 40	55.0	8.0	1 - 4
<b>SKINTOP® CLICK-R black</b>								
53112929	CLICK-R 12	1 - 5	12.3 (-0.2)		15 / 18	40.0	8.0	1 - 4
53112885	CLICK-R 16	4 - 7	16.3 (-0.2)		19 / 22	42.0	8.0	1 - 4
53112886	CLICK-R 20	5 - 10	20.3 (-0.2)		25 / 27	45,5	8.0	1 - 4
53112887	CLICK-R 25	6 - 13	25.3 (-0.2)		30 / 34	48,5	8.0	1 - 4
53112931	CLICK-R 32	7 - 15	32.3 (-0.2)		36 / 40	55.0	8.0	1 - 4

U.I. Lapp GmbH	<b>PRODUCT INFORMATION</b>	 <b>LAPP GROUP</b>
	<b>SKINTOP® CLICK-R</b>	12.09.2012



Product Management	Document: LAPP_PRO26625EN.pdf	3 / 3
--------------------	-------------------------------	-------