


**MSVD POWER SOCKET NEMA (GFCI)**

Mounting rail

USA (2 × NEMA-GFCI 5-15)  
(Ground Fault Circuit Interrupter)  
Screw terminals  
LED (yellow)

Each socket can be loaded with 15 A, however, the total load of both sockets must be below 30 A.

[Link to Product](#)**Illustration**

Product may differ from Image

**Approvals****Technical Data**

Operating voltage	max. 125 V AC
Operating current	max. 15 A
Trip level	4...6 mA

**General data**

Mounting method	DIN-rail mountable (EN 60715)
Connection	Screw terminals: max. 6 mm <sup>2</sup>
Dimensions H × W × D	126×64×55 mm

**Commercial data**

country of origin	CZ
customs tariff number	85369010
minimum order quantity	1