

Toledo Mirage E115

ToLEDo Mirage E115 105LM E27 SL
0029944



Product features

- A perfect choice for hospitality, decorative and mood lighting applications
- Unique and innovative lamp design and construction
- Low-lumen output to create the low-lit effect and gives no glare
- Low power construction: only 2.5W
- Perfect for SylPendant fixtures - a range of unique and elegant E27 lamp pendants, available in copper, brass, black and white finish
- Candlelight 2000K colour temperature creates a warm and cosy ambience
- High colour rendering - CRI80
- High quality, scratch and temperature resistant golden tinted glass envelope
- 25,000 hours of average rated life. Last 25 times longer than incandescent lamps
- Omni-directional light distribution
- Non-dimmable
- More than 100,000X switching cycles
- 3 years warranty



PRODUCT OVERVIEW

| | |
|---------------------------------|---------------------------------|
| Product name | ToLEDo Mirage E115 105LM E27 SL |
| Technology | LED |
| Watt (Rated) (W) | 2.5 |
| Type | LED exchangeable |
| Cap/Base | E27 |
| Fixture rating | Open |
| General application | Residential & Consumer |
| ETIM Class | EC001959 |
| E-number FI | 4740683 |
| Warranty | 3 years |
| Luminous flux (lm) | 105 |
| Colour temperature (K) | 2000 |
| Light colour | Candlelight |
| CRI (Ra) | 80 |
| Colour Variation Initial (SDCM) | SDCM6 |
| Photobiological Risk Group | RG0 |
| Wattage (W) | 2.5 |
| Product Voltage (V) | 230 |
| Dimmable | No |
| Average life (Nominal) (h) | 25000 |
| Product EAN number | 5410288299440 |

DATA TABLE

General data

| | |
|------------------|---------------------------------|
| Product name | ToLEDo Mirage E115 105LM E27 SL |
| Technology | LED |
| Watt (Rated) (W) | 2.5 |

Toledo Mirage E115

ToLEDo Mirage E115 105LM E27 SL

0029944

| | |
|---|------------------------|
| Type | LED exchangeable |
| Cap/Base | E27 |
| Fixture rating | Open |
| General application | Residential & Consumer |
| Operating temperature range (°C) | -20°C...+40°C |
| Performance ambient temperature Tq (°C) | 25 |
| ETIM Class | EC001959 |
| E-number FI | 4740683 |
| Warranty | 3 years |

Optical data

| | |
|--|-------------|
| Luminous flux (lm) | 105 |
| Luminous flux (Rated) (lm) | 105 |
| Colour temperature (K) | 2000 |
| Light colour | Candlelight |
| CRI (Ra) | 80 |
| Colour Variation Initial (SDCM) | SDCM6 |
| Photobiological Risk Group | RG0 |
| Lumen maintenance at end of nominal life (%) | 70 |

Electrical data

| | |
|---|---------|
| Wattage (W) | 2.5 |
| Equivalent watt (W) | 12 |
| Starting time (max) (s) | 0.5 |
| Warm-up time to 60% of full light (max) (s) | 1 |
| Product Voltage (V) | 230 |
| Lamp power factor | 0.5 |
| Control gear required | No |
| No. of switching cycles before premature failures | >100000 |
| Transformer required | No |
| Dimmable | No |
| Inrush Current (A) | 0.2 |
| Inrush Duration (µs) | 8000 |
| Lamp Energy Label (class) | G |
| kWh per 1000 hours burning time | 3 |
| Nominal Frequency (Hz) | 50/60Hz |

Lifetime data

| | |
|----------------------------|-------|
| Lifespan L70 B50 | 25000 |
| Average life (Nominal) (h) | 25000 |
| Average life (Rated) (h) | 25000 |

Physical data

| | |
|-------------------------------|------|
| Nominal Product Length (mm) | 347 |
| Nominal Product Diameter (mm) | 116 |
| Weight (kg) | 0.29 |

Toledo Mirage E115

ToLEDo Mirage E115 105LM E27 SL

0029944


Packaging

| | |
|---------------------------------------|----------------|
| Single packaging type | Carton |
| Product EAN number | 5410288299440 |
| Packaging single length / height (cm) | 37.0 |
| Packaging single width (cm) | 12.6 |
| Packaging single depth (cm) | 12.6 |
| DUN14 (outer) | 15410288299447 |
| Units per outer package | 4 |
| Packaging outer length / height (cm) | 27.0 |
| Packaging outer width (cm) | 27.0 |
| Packaging outer depth (cm) | 39.5 |

Safety data

| | |
|-------------------------------------|--|
| Optimal operating condition (°C) | -20-40 |
| Breakage cleaning instructions | Not applicable |
| Special purpose lamp | No |
| Dry applications use only | Yes |
| Suitable for household illumination | Yes |
| Safety message | Not Suitable for totally enclosed fixtures |


PHOTOMETRY




TECHNICAL DRAWINGS

SYLVANIA

Toledo Mirage E115
ToLEDo Mirage E115 105LM E27 SL
0029944



0029944



3
kWh/1000h




2019/2015

SYLVANIA

Toledo Mirage E115
ToLEDo Mirage E115 105LM E27 SL
0029944



0029944



3
kWh/1000h



2019/2015